



Dichroic


Dichroic-Strukturen / Dichroic-structures




35 347 xx




35 342 xx



35 346 xx




35 357 xx



35 348 xx



35 345 xx



35 359 xx

Notes on the Care and Handling of Dichroic Glass:

The coating on Dichroic glass is vulnerable to scratches and damage from solvents, oils, adhesives, and fluxes. Therefore, the glass should be handled carefully and protected from abrasions. When necessary, Dichroic glass can be cleaned using mild soap and water or a mild glass cleaner and dried with a soft cloth.

Leaded Glass Application

When fabricating a panel designed to include Dichroic glass, use a cutter without oil, and score the glass on the uncoated side. The coating can be protected from soldering and grouting phases by covering it with low tack tape or contact paper that is easily removed when finished (be sure to test first with a small scrap piece of glass).

Lamination Application

Some Dichroic jewels and bevels are made by laminating the clear bevel to a coated sheet of thin float glass. This process layers the coating between the glass and the jewel, and thus it is protected from the dangers listed above.

Fused Glass Application

Fusing Dichroic glass not only produces captivating effects, it eliminates all the vulnerabilities listed above as well. The fusing process molecularly binds the glass and the coating materials. Reflective colors difficult to perceive on clear glass will intensify when fused onto a background of black glass. Clear glass offers versatility as it can be fused with Dichroic coating either up or down. When fused Dichroic side down, the coating will be encased in a layer of clear. When fused Dichroic side up, a soft metallic effect is achieved.

Anmerkungen zum Umgang und zur Behandlung des Dichroic Glases:

Die Schicht auf Dichroic Glas ist anfällig für Kratzer und für die Beschädigung durch Lösungsmitteln, Öle, Kleber und Flussmittel. Folglich sollte das Glas sorgfältig angefasst werden und vor Abnutzungen geschützt werden. Falls notwendig kann Dichroic Glas mit milder Seife und Wasser oder einem milden Glasreinigungsmittel gesäubert werden und mit einem weichen Tuch getrocknet werden.

Bei Arbeiten mit Dichroic Glas, benutzen Sie bitte einen Glasschneider ohne Öl, und schneiden Sie das Glas auf der unbeschichteten Seite. Die Schicht kann vor den lötfenden und überziehenden Phasen geschützt werden, indem man es mit dünnen Klebeband oder Kontaktpapier bedeckt, das leicht entfernt werden kann, wenn es fertig gestellt ist. (Vor der Entfernung an einem kleinen Reststück Glas prüfen).

Einige Dichroic-Muggelsteine und Facetten werden hergestellt, indem man die klare Facette mit einer überzogenen Schicht des dünnen Floatglases laminiert. Dieser Prozeß überlagert die Schicht zwischen dem Glas und dem Muggelstein, und wird folglich vor den Gefahren geschützt, die oben beschrieben werden.

Das Fusen von Dichroic Glas produziert nicht nur faszinierende Effekte, es beseitigt auch die ganzen Anfälligkeiten, die oben beschrieben werden. Der Fusingprozeß bindet molekular das Glas und die beschichteten Materialien. Die reflektierenden Farben, die schwierig auf freiem Glas wahrzunehmen sind verstärkt, wenn sie auf einen Hintergrund von schwarzen Glas fixiert werden. Klares Glas bietet eine vielseitige Verwendbarkeit, weil es mit der Dichroic Schicht entweder oben oder unten geschmolzen werden kann. Wenn die Dichroic Seite unten geschmolzen ist, wird die Beschichtung in einer Schicht von klaren Glas eingehüllt. Wenn die Dichroic Seite oben fixiert ist, wird ein weicher metallischer Effekt erreicht.



35 330 10 magenta - teal
Farbwechsel von Dichroic-
Glas unter veränderten
Blickwinkeln.
Changing the angle of
viewing results in varying
color combinations.

Wichtige Information für die Verarbeitung von Dichroic Gläsern

Beim Verschmelzen von
identischen Dichroic Gläsern kann
es zu Farbabweichungen im
Endprodukt kommen.

Important information for working with dichroic glass:

When fusing identical dichroic
glasses, color deviations can occur
in the final product.

Was ist Dichroic Glas :

Dichroic ist eine high-tech optische
Schicht, die selektiv bestimmte
Wellenlängen (Farben) des Lichtes
reflektiert und die restlichen
Wellenlängen durchpassen läßt.
Dieser gleiche Effekt wird in der
Natur in Pfaufedern und Opalen
gesehen. Das Wort "Dichroic"
bedeutet zwei Farben, welches
sich auf die übertragene Farbe und
reflektierte Farbe bezieht. Der
beschichtende Prozeß erfolgt in
einem hohen Vakuumraum, der
einige Spezialgeräte als Ausrüstung
hat um den beschichtenden
Prozess zu steuern und zu
überwachen.

What is Dichroic Glass:

Dichroic is a high-tech optical
coating that selectively reflects
certain wavelengths (colors) of light
and allows the remaining
wavelengths to transmit through.
This same effect is seen in nature in
peacock feathers and opals. The
word "dichroic" means two colors,
which refers to transmitted color
and reflected color. The coating
process is done in a high vacuum
chamber that has several pieces of
specialized equipment to control
and monitor the coating process.

Da der Charakter des Dichroic-
Glases der Wechsel ist, ist es nahezu
unmöglich diese Gläser farblich im
Katalog abzubilden. Um Ihnen das
Prinzip des Glases zu demonstrieren
haben wir in einer Bilderfolge ein
Glas in verschiedenen Winkeln
fotografiert. Wie Sie sehen, könnte
jedes Foto auch für ein anderes Glas
stehen. Dichroic-Gläser sollten Sie
niemals in einer Serie einsetzen wo
ein Stück wie das andere sein soll.
Dichroic-Gläser sollten Sie immer
wie ein Stück Einmaligkeit einsetzen.

The character of dichroic glass is its
changeability, which means that it is
nearly impossible to illustrate this
product on a color catalog page. To
demonstrate the principle of dichroic
glass, we have taken a series of
photos viewed from various angles.
As you see, each Foto could be the
image of a totally different glass.
Dichroic glass should not be used for
a series where one piece is to
resemble the next. Dichroic glass
should always be used to represent a
piece of uniqueness.


Beschreibung / Description

35 308 xx - 35 309 xx = AK104
35 310 xx - 35 319 xx = System 96
35 320 xx - 35 359 xx = AK 90
35 360 xx = Float

35 330 xx
 Basisglas klar, 1,5 mm
 Basic glass clear, 1,5 mm

35 340 xx
 Basisglas schwarz, 1,5 mm
 Basic glass black, 1,5 mm

Basisglas schwarz / Basic glass black:
 35 342 xx Rippel 4,0 mm
 35 345 xx Rippel gekämmt 4,0 mm
 35 346 xx Granite 3,0 mm
 35 347 xx Fibroid 1,5 mm
 35 348 xx genoppt 1,5 mm
 35 356 xx Waben 1,5 mm
 35 357 xx Punkte 1,5 mm
 35 358 xx Ufo 1,5 mm
 35 359 xx Quadrat 1,5 mm
 35 360 xx Float 1,0 mm



RB 1

AK 104

35 308 20 Dichroic
Moretti
BG: schwarz/black
R: regenbogen/rainbow,
3,0 mm



760 CR

AK 104

35 309 18 Dichroic
Moretti
BG: klar/clear
R: regenbogen/rainbow
3,0 mm



BP 1

AK 104

35 309 20 Dichroic
Moretti
BG: klar/clear
R: regenbogen/rainbow
3,0 mm



540 YB

System 96


35 310 02 Dichroic
BG: S1009
schwarz / black
R: blau /blue
1,5 mm



575 PT

System 96

35 310 08 Dichroic
BG: S1009
schwarz/ black
R: teal /teal
2,0 mm



615 MG

System 96


35 310 10 Dichroic
BG: S1009
schwarz/ black
R: türkis/turquoise
2,0 mm



660 BG

System 96


35 310 14 Dichroic
BG: S1009
schwarz / black
R: grün /green
2,0 mm



710 CC

System 96

35 310 16 Dichroic
BG: S1009
schwarz / black
R: gelb / yellow
2,0 mm



760 CR

System 96

35 310 18 Dichroic
BG: S1009
schwarz / black
R: gold / gold
2,0 mm



RB 1

System 96


35 310 20 Dichroic
BG: S1009
schwarz / black
R: regenbogen /rainbow
2,0 mm



GM

System 96

35 310 22 Dichroic
BG: S1009
schwarz / black
R: rosa / pink
2,0 mm



silber

System 96

35 310 26 Dichroic
BG: S1009
schwarz / black
R: silber / silver
2,0 mm



810 CX

System 96


35 310 34 Dichroic
BG: S1009
schwarz / black
R: kupfer/cooper
2,0 mm



RB 2

System 96


35 310 36 Dichroic
BG: S1009
schwarz / black
R: regenbogen/rainbow
2,0 mm



S-CA-R

System 96


35 310 40 Dichroic
BG: S1009
schwarz / black
R: kupferrot /cooper red
2,0 mm



S-BL-C

System 96


35 310 42 Dichroic
BG: S1009
schwarz / black
R: kirsche /cherry
2,0 mm



salmon

System 96


35 310 44 Dichroic
BG: S1009
schwarz / black
R: lachs/salmon
2,0 mm



violet

System 96


35 310 46 Dichroic
BG: S1009
schwarz / black
R: lila/violet
2,0 mm



Emeral

System 96

35 310 48 Dichroic
BG: S1009
schwarz / black
R: grün /green
2,0 mm

























Purple

System 96





35 310 50 Dichroic
BG: S1009
schwarz / black
R: lila/violet
2,0 mm

DICHROIC GLAS / DICHROIC GLASS




Box	 35 310 60 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm	Box I	 35 310 61 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm	Ballon	 35 310 62 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm	Ball I	 35 310 63 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm
Dot I	 35 310 64 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm	Dot 2	 35 310 65 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm	Dot 3	 35 310 66 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm	Quadrat	 35 310 67 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm
Quadrat I	 35 310 68 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm	Quadrat 2	 35 310 69 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm	Quadrat 3	 35 310 70 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm	Streine	 35 310 71 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm
Marquis	 35 310 72 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm	Marquis 2	 35 310 73 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm	Waben	 35 310 74 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm	RBA	 35 310 75 Dichroic BG: S1009 schwarz/black R: Design/pattern 2,0 mm
	 35 310 97 Dichroic Mustersatz/ Sample-Set 23 Muster 4 x 4 cm schwarz/black 2,0 mm		 35 310 98 Dichroic Mustersatz/ Sample-Set, 16 Muster 4 x 4 cm schwarz/black 2,0 mm		 35 310 99 Dichroic Mustersatz/ Sample-Set, 23 Muster 4 x 4 cm klar/clear 2,0 mm	UBFP-RBI	 35 311 20 Dichroic BG: (U51-56) schwarz/black R: regenbogen / rainbow 2,0 mm
RB I	 35 312 20 Dichroic BG: S1009 schwarz/black R: regenbogen/rainbow 2,0 mm	RB I	 35 313 20 Dichroic BG: S100W klar / clear R: regenbogen/rainbow 2,0 mm	RB I	 35 314 20 Dichroic BG: S100R klar / clear R: regenbogen/rainbow 2,0 mm	RB I	 35 315 20 Dichroic BG: S100H klar / clear R: regenbogen/rainbow 2,0 mm
RB I	 35 316 20 Dichroic BG: S100GG klar / clear R: regenbogen/rainbow 2,0 mm	UCF-RB	 35 317 20 Dichroic BG: (U 70-00) klar / clear R: regenbogen/rainbow 2,0 mm	RB I	 35 318 20 Dichroic BG: S100G klar / clear R: regenbogen/rainbow 2,0 mm	UCFP-RB I	 35 319 20 Dichroic BG: (U51-00) klar / clear R: regenbogen/rainbow 2,0 mm

FLACHGLAS / FLAT GLASS

540 YB		35 320 02 Dichroic BTB 0100-50 BG: schwarz/black R: blau/blue, 1,5 mm
475 YV		35 320 04 Dichroic BTB 0100-50 BG: schwarz/black R: violet/violet, 1,5 mm
500 YP		35 320 06 Dichroic BTB 0100-50 BG: schwarz/black R: lila/purple, 1,5 mm
575 PT		35 320 08 Dichroic BTB 0100-50 BG: schwarz/black R: teal/teal, 1,5 mm
615 MG		35 320 10 Dichroic BTB 0100-50 BG: schwarz/black R: türkis/turquoise, 1,5 mm
660 BG		35 320 14 Dichroic BTB 0100-50 BG: schwarz/black R: grün/green, 1,5 mm
710 CC		35 320 16 Dichroic BTB 0100-50 BG: schwarz/black R: gelb/yellow, 1,5 mm
760 CR		35 320 18 Dichroic BTB 0100-50 BG: schwarz/black R: gold/gold, 1,5 mm
15RBI		35 320 20 Dichroic BTB 0100-50 BG: schwarz/black R: regenb./rainbow, 2,0 mm
G/M		35 320 22 Dichroic BTB 0100-50 BG: schwarz/black R: rosa/pink, 1,5 mm
G/P		35 320 24 Dichroic BTB 0100-50 BG: schwarz/black R: rosa/pink, 1,5 mm
silver		35 320 26 Dichroic BTB 0100-50 BG: schwarz/black R: silber/silver, 1,5 mm
b-silber		35 320 28 Dichroic BTB 0100-50 BG: schwarz/black R: blau silber/blue silver, 1,5
G/M/B		35 320 32 Dichroic BTB 0100-50 BG: schwarz/black R: hellblau/light blue, 1,5
810CX		35 320 34 Dichroic BTB 0100-50 BG: schwarz/black R: kupfer/copper, 1,5
Rb2		35 320 36 Dichroic BTB 0100-50 BG: schwarz/black R: regenb./rainbow, 1,5 mm
C-A Red		35 320 40 Dichroic BTB 0100-50 BG: schwarz/black R: K-rot/K-red, 1,5 mm
B-Cherry		35 320 42 Dichroic BTB 0100-50 BG: schwarz/black R: kirsche/cherry, 1,5 mm
Salmon		35 320 44 Dichroic BTB 0100-50 BG: schwarz/black R: lachs/salmon, 1,5 mm
Violet		35 320 46 Dichroic BTB 0100-50 BG: schwarz/black R: lila violett, 1,5 mm
Emerald		35 320 48 Dichroic BTB 0100-50 BG: schwarz/black R: grün/green, 1,5 mm
Emerald		35 320 49 Dichroic BTB 1101-50 BG: klar/clear R: grün/green, 1,5 mm
Purple		35 320 50 Dichroic BTB 0100-50 BG: schwarz/black R: violet/purple, 1,5 mm
Boxes 2		35 320 60 Dichroic BTB 0100-50 BG: schwarz/black R: Design/Pattern 1,5 mm
Boxes 1		35 320 61 Dichroic BTB 0100-50 BG: schwarz/black R: Design/Pattern, 1,5 mm
Ballon 3		35 320 62 Dichroic BTB 0100-50 BG: schwarz/black R: Design/Pattern, 1,5 mm
Ballon 1		35 320 63 Dichroic BTB 0100-50 BG: schwarz/black R: Design/Pattern, 1,5 mm
Punkte 1		35 320 64 Dichroic BTB 0100-50 BG: schwarz/black R: Design/Pattern, 1,5 mm


DICHROIC GLAS / DICHROIC GLASS



35 320 65 Dichroic
BTB 0100-50
BG: schwarz / black
R: Design/Pattern, 1,5 mm



35 320 69 Dichroic
BTB 0100-50
BG: schwarz / black
R: Design/Pattern, 1,5 mm




35 320 73 Dichroic
BTB 0100-50
BG: schwarz / black
R: Design/Pattern, 1,5 mm




35 320 86 Pinwheels
1,5mm
10 Stck 1,5 cm auf Karte
10 pcs 1,5 cm on cardboard




35 322 20 Dichroic
(I 101-53) 1,5 mm
BG: klar / clear
R: regenbogen/rainbow,



35 329 20 Dichroic
(U 50-00) 3,0 mm
BG: klar / clear
R: regenbogen/rainbow,




35 330 08 Dichroic
(U 61-00) 1,5 mm
BG: klar / clear
R: pink,türkis pink,turquoise



35 320 66 Dichroic
BTB 0100-50
BG: schwarz / black
R: Design/Pattern, 1,5 mm



35 320 70 Dichroic
BTB 0100-50
BG: schwarz / black
R: Design/Pattern, 1,5 mm




35 320 74 Dichroic
BTB 0100-50
BG: schwarz / black
R: Design/Pattern, 1,5 mm



35 320 97 Dichroic
Mustersatz, 23 Muster 4x4cm
auf schwarz, Sample Set,
23 Samples 4x4cm on black




35 323 20 Dichroic
(I 101-53) 1,5 mm
BG: klar / clear
R: regenbogen/rainbow,




35 330 02 Dichroic
(U 61-00) 1,5 mm
BG: klar / clear
R: gelb,blau/yellow,blue




35 330 10 Dichroic
(U 61-00) 1,5 mm
BG: klar / clear
R: magenta,teal/magenta,teal



35 320 67 Dichroic
BTB 0100-50
BG: schwarz / black
R: Design/Pattern, 1,5 mm




35 320 71 Dichroic
BTB 0100-50
BG: schwarz / black
R: Design/Pattern, 1,5 mm




35 320 75 Dichroic
BTB 0100-50
BG: schwarz / black
R: Design/Pattern, 1,5 mm



35 320 98 Dichroic
Mustersatz, 16 Muster 4x4cm
auf schwarz, Sample Set,
16 Samples 4x4cm on black




35 326 20 Dichroic
(U 65-00) 3,0 mm
BG: klar / clear
R: regenbogen/rainbow,



35 330 04 Dichroic
(U 61-00) 1,5 mm
BG: klar / clear, R: hellgelb,
ultraviolett/yellow,ultraviolet



35 330 12 Dichroic
(U 61-00) 1,5 mm
BG: klar / clear
R: violett,grün/violet,green



35 320 68 Dichroic
BTB 0100-50
BG: schwarz / black
R: Design/Pattern, 1,5 mm




35 320 72 Dichroic
BTB 0100-50
BG: schwarz / black
R: Design/Pattern, 1,5 mm




35 320 85 Pinwheels
1,5mm
20 Stck 1,0 cm auf Karte
20 pcs 1,0 cm on cardboard



35 320 99 Dichroic
Mustersatz, 23 Muster 4x4cm
auf klar, Sample Set,
23 Samples 4x4cm on clear



35 327 20 Dichroic
(U 70-00) 3,0 mm
BG: klar / clear
R: regenbogen/rainbow,



35 330 06 Dichroic
(U 61-00) 1,5 mm
BG: klar / clear, R: amber,
hellblau/amber, light blue



35 330 14 Dichroic
(U 61-00) 1,5 mm
BG: klar / clear
R: blau,gelb/blue,yellow

FLACHGLAS / FLAT GLASS



UTC-LB

35 330 16 Dichroic
(U 61-00) BG: klar /clear
R: hellblaugold, light blue
gold, 1,5 mm



UTC-TE

35 330 24 Dichroic
(U 61-00) BG: klar /clear
R: teal hellrosa/teal light pink
1,5 mm




UTC-MR

35 330 32 Dichroic
(U 61-00) BG: klar /clear
R: hellgrün, magenta/
light green, magenta 1,5 mm



UTB-AM

35 340 06 Dichroic
(U 61-56)
BG: schwarz/black
R: hellbl./light blue, 1,5 mm



UTB-BL

35 340 14 Dichroic
(U 61-56)
BG: schwarz/black
R: gelb /yellow 1,5 mm



UTB-GR

35 340 22 Dichroic
(U 61-56)
BG: schwarz/black
R: rosa /pink, 1,5 mm



UTB-RE

35 340 30 Dichroic
(U 61-56)
BG: schwarz/black
R: hellcyan/light cyan, 1,5 mm




UTC-CY

35 330 18 Dichroic
(U 61-00) BG: klar /clear
R: cyan kupfer /cyan kupfer
1,5 mm



UTC-TQ

35 330 26 Dichroic
(U 61-00) BG: klar /clear
R: türkis, silber/rosagold/
turquoise, silver, 1,5 mm




UTC-RR

35 330 34 Dichroic
(U 61-00)
BG: klar /clear
R: rot/red, 1,5 mm




UTB-PI

35 340 08 Dichroic
(U 61-56)
BG: schwarz/black
R: türkis/light blue, 1,5 mm



UTB-LB

35 340 16 Dichroic
(U 61-56)
BG: schwarz/black
R: gold /gold, 1,5 mm



UTB-TE

35 340 24 Dichroic
(U 61-56)
BG: schwarz/black
R: hellrosa / light pink, 1,5




UTB-MR

35 340 32 Dichroic
(U 61-56)
BG: schwarz/black
R: magenta/ magenta, 1,5 mm



UTC-RB

35 330 20 Dichroic
(U 61-00) BG: klar /clear
R: cyan kupfer /cyan kupfer
1,5 mm



UTC-OR

35 330 28 Dichroic
(U 61-00) BG: klar /clear
R: orange, cyan/orange, cyan
1,5 mm



UTB-YE

35 340 02 Dichroic
(U 61-56)
BG: schwarz/black
R: blau /blue, 1,5 mm



UTB-MA

35 340 10 Dichroic
(U 61-56)
BG: schwarz/black
R: teal /teal 1,5 mm



UTB-CY

35 340 18 Dichroic
(U 61-56)
BG: schwarz/black
R: kupfer/copper, 1,5 mm




UTB-TQ

35 340 26 Dichroic
(U 61-56)
BG: schwarz/black
R: silber, rosa/silver pink 1,5



UTB-RR

35 340 34 Dichroic
(U 61-56)
BG: schwarz/black
R: rot / red, 1,5 mm



UTC-GR

35 330 22 Dichroic
(U 61-00) D: klar /clear
R: rosa, grün /pink, green
1,5 mm



UTC-RE

35 330 30 Dichroic
(U 61-00) BG: klar /clear
R: rot, hellcyan/red, light cyan
1,5 mm



UTB-LY

35 340 04 Dichroic
(U 61-56)
BG: schwarz/black
R: ultraviolett/ ultraviolet 1,5



UTB-VI

35 340 12 Dichroic
(U 61-56)
BG: schwarz/black
R: grün /green, 1,5 mm



UTB-RB

35 340 20 Dichroic
(U 61-56)
BG: schwarz/black
R: regenb./rainbow, 1,5 mm



UTB-OR

35 340 28 Dichroic
(U 61-56)
BG: schwarz/black
R: cyan /cyan 1,5 mm




UTB-PR

35 340 36 Dichroic
(U 61-56)BG: schwarz/black
R: UPre. Regenbogen/
UPremium Rainbow, 1,5 mm




UTB-VR 35 340 38 Dichroic (U 61-56) 1,5 mm BG:schwarz/black R:UPrem.pink-lila /Ultr.Ppink-violet	UTB-XR 35 340 40 Dichroic (U 61-56) 1,5 mm BG:schwarz/black R:U.Prem. rot /Ultra P. red	UBR-MA 35 342 10 Dichroic (U 61-56) 1,5 mm BG:schwarz/black R:teal Rip/teal Rip	UBR-BL 35 342 14 Dichroic (U 51-56) 3,0 mm BG: schwarz/black R: gelb Rip/yellow Rip
UBR-CY 35 342 18 Dichroic (U 51-56) 3,0 mm BG:schwarz/black R: kupfer Rip/copper Rip	UBR-RB 35 342 20 Dichroic (U 51-56) 3,0 mm BG:schwarz/black R: regenb. Rip/rainbow Rip	UBR-RB 35 342 21 Dichroic (U 51-00) 3,0 mm BG: klar/clear R: regenb. Rip/rainbow Rip	UCR-MR 35 342 33 Dichroic (U 51-00) 3,0 mm BG: klar/clear R: magenta Rip/magenta Rip
UBR-RR 35 342 34 Dichroic (U 51-56) 3,0 mm BG: schwarz/black R: rot Rip /red Rip	UBR-VR 35 342 38 Dichroic (U 51-56) 3,0 mm BG:schwarz/black R: violet Rip/violet Rip	UBFP-YE 35 345 02 Dichroic (U 57-56) 3,0 mm BG: schwarz/black R: blau Fripp/blue Fripp	UBFP-LB 35 345 16 Dichroic (U 57-56) 3,0 mm BG: schwarz/black R: gold/gold
UBFP-CY 35 345 18 Dichroic (U 57-56) 3,0 mm BG: schwarz/black R: kupfer Fripp/cooper Fripp	UBFP-TQ 35 345 26 Dichroic (U 57-56) 3,0 mm BG: schwarz/black R: silber-rosa/silver pink	UBFP-RE 35 345 30 Dichroic (U 57-56) 3,0 mm BG: schwarz/black R: hellcyan/light cyan	UBG-MA 35 346 10 Dichroic (U 65-56) 3,0 mm BG: schwarz/black R: teal/teal
UBG-BL 35 346 14 Dichroic (U 65-56) 3,0 mm BG: schwarz/black R: gelb / yellow	UBG-CY 35 346 18 Dichroic (U 65-56) 3,0 mm BG: schwarz/black R: kupfer/cooper	UBG-RB 35 346 20 Dichroic (U 65-56) 3,0 mm BG: schwarz/black R: regenbogen /rainbow	UBG-TQ 35 346 26 Dichroic (U 65-56) 3,0 mm BG: schwarz/black R: silber rosa /silver pink
UBG-RR 35 346 34 Dichroic (U 65-56) 3,0 mm BG: schwarz/black R: rot /red	UBF-MA 35 347 10 Dichroic (U 70-56) 3,0 mm BG: schwarz/black R: teal /teal	UBF-VI 35 347 12 Dichroic (U 70-56) 3,0 mm BG: schwarz/black R: grün /green	UBF-RB 35 347 20 Dichroic (U 70-56) 3,0 mm BG:schwarz/black R: regenbogen /rainbow
UBF-XR 35 347 40 Dichroic (U 70-56) 3,0 mm BG: schwarz/black R: extra rot /extra red	UBRA-MA 35 348 10 Dichroic (U 81-56) 3,0 mm BG: schwarz/black R: teal Radium /teal Radium	UBRA-BL 35 348 14 Dichroic (U 81-56) 3,0 mm BG: schwarz/black R: gelb Radium /yellow Radium	UBRA-CY 35 348 18 Dichroic (U 81-56) 3,0 mm BG: schwarz/black R: kupfer Radium/copper Radium



UBRA-RB

AK 90

35 348 20 Dichroic
(U 81-56) 1,5 mm
BG: schwarz/black
R: regenbogen/rainbow



Waben LB

AK 90


35 356 16 Dichroic
(U 61-56) 1,5 mm
BG: schwarz/black
R: gold/gold



Punkte-CY

AK 90


35 357 19 Dichroic
(U 61-00) 1,5 mm
BG: klar/clear
R: kupfer/copper



Quadrat-PI

AK 90


35 359 08 Dichroic
(U 61-56) 1,5 mm
BG: schwarz/black
R: türkis/turquoise



FD-LY

AK 82

35 360 04 Dichroic
BG: klar / clear 1,0 mm
R: gelb,blau/yellow,blue



FD-VI

AK 82


35 360 12 Dichroic
BG: klar / clear 1,0 mm
R: violett,grün/violet,green



FD-RB

AK 82


35 360 20 Dichroic
BG: klar / clear 1,0 mm
R: regenbogen/rainbow



UBRA-TE

AK 90


35 348 24 Dichroic
(U 81-56) 1,5 mm
BG: schwarz/black
R: hellrosa/light pink



Punkte-PI

AK 90


35 357 08 Dichroic
(U 61-56) 1,5 mm
BG: schwarz/black
R: türkis/turquoise



Punkte-RR

AK 90


35 357 34 Dichroic
(U 61-56) 1,5 mm
BG: schwarz/black
R: rot/red



Quadrat-CY

AK 90

35 359 18 Dichroic
(U 61-56) 1,5 mm
BG: schwarz/black
R: kupfer/copper



FD-AM

AK 82

35 360 06 Dichroic
BG: klar / clear 1,0 mm
R: hellamber ultrav./
lightamber ultrav.



FD-BL

AK 82


35 360 14 Dichroic
BG: klar / clear 1,0 mm
R: blau,gelb / blue,yellow



FD-GR

AK 82

35 360 22 Dichroic
BG: klar / clear 1,0 mm
R: grün,rosa/green,pink



Waben VI

AK 90


35 356 12 Dichroic
(U 61-56) 1,5 mm
BG: schwarz/black
R: grün/green



Punkte-VI

AK 90


35 357 13 Dichroic
(U 61-00) 1,5 mm
BG: klar/clear
R: violett,grün/violet,green



Ufo-MA

AK 90


35 358 10 Dichroic
(U 61-56) 1,5 mm
BG: schwarz/black
R: teal /teal



Waben BL

AK 90


35 356 14 Dichroic
(U 61-56) 1,5 mm
BG: schwarz/black
R: gelb/yellow



Punkte-CY

AK 90


35 357 18 Dichroic
(U 61-56) 1,5 mm
BG: schwarz/black
R: kupfer/copper



UFO-LB

AK 90

35 358 16 Dichroic
(U 61-56) 1,5 mm
BG: schwarz/black
R: gold /gold



FD-YE

AK 82


35 360 02 Dichroic
BG: klar / clear 1,0 mm
R: gelb,blau/yellow,blue



FD-MA

AK 82

35 360 10 Dichroic
BG: magenta,tea 1,0 mm
R: gelb,blau/yellow,blue



FD-CY

AK 82

35 360 18 Dichroic
BG: klar / clear 1,0 mm
R: cyan,kupfer/cyan, copper












FD-TQ

AK 82

35 360 26 Dichroic
BG: klar / clear 1,0 mm
R: türkis,silb/rosa/turquoise,
silver, pink

DICHROIC GLAS / DICHROIC GLASS



FD-OR		35 360 28 Dichroic BG: klar / clear 1,0 mm R: orange, cyan/orange, cyan
FD-RE		35 360 30 Dichroic BG: klar / clear 1,0 mm R: rot, hellcyan/red, light cyan
FD-MR		35 360 32 Dichroic BG: klar / clear 1,0 mm R: hellgrün, magenta/ light green, magenta
FD-RR		35 360 34 Dichroic BG: klar / clear 1,0 mm R: rot / red
UBR-TE		35 342 24 Dichroic (U 51-56) 3,0 mm BG: schwarz / black R: hellrosa / light pink
UCR-TE		35 342 25 Dichroic (U 51-00) 3,0 mm BG: klar / clear R: hellrosa / light pink
UBR-OR		35 342 28 Dichroic (U 51-56) 3,0 mm BG: schwarz / black R: cyan / cyan
UCR-OR		35 342 29 Dichroic (U 51-00) 3,0 mm BG: klar / clear R: cyan / cyan
UBM-MR		35 342 32 Dichroic (U 51-56) 3,0 mm BG: schwarz / black R: magenta / magenta
UCR-RR		35 342 35 Dichroic (U 51-00) 3,0 mm BG: klar / clear R: rot Rip / red Rip
UCG-BL		35 346 07 Dichroic (U 65-00) 3,0 mm BG: klar / clear R: hellblau / light blue
UCG-BL		35 346 15 Dichroic (U 65-00) 3,0 mm BG: klar / clear R: gelb / yellow
UCG-TQ		35 346 27 Dichroic (U 65-00) 3,0 mm BG: klar / clear R: silber-rosa / silver pink
UBG-OR		35 346 28 Dichroic (U 65-56) 3,0 mm BG: schwarz / black R: cyan / cyan
UCG-OR		35 346 29 Dichroic (U 65-00) 3,0 mm BG: klar / clear R: cyan / cyan
UBG-MR		35 346 32 Dichroic (U 65-56) 3,0 mm BG: schwarz / black R: magenta / magenta
UBF-LB		35 347 16 Dichroic (U 70-56) 3,0 mm BG: schwarz / black R: gold / gold
UBF-CY		35 347 18 Dichroic (U 70-56) 3,0 mm BG: schwarz / black R: kupfer / cooper
UBFP-OR		35 347 28 Dichroic (U 70-56) 3,0 mm BG: schwarz / black R: cyan / cyan
UBF-MR		35 347 32 Dichroic (U 70-56) 3,0 mm BG: schwarz / black R: magenta / magenta
UCRA-AM		35 348 07 Dichroic (U 80-00) 3,0 mm BG: klar / clear R: hellblau / light blue
UCRA-OR		35 348 29 Dichroic (U 80-00) 3,0 mm BG: klar / clear R: cyan / cyan
UCRA-MR		35 348 33 Dichroic (U 80-00) 3,0 mm BG: klar / clear R: magenta / magenta
WABEN-RB		35 356 20 Dichroic (U 60-56) 3,0 mm BG: schwarz / black R: regenbogen / rainbow
Punkte-RB3		35 357 20 Dichroic (U 60-56) 3,0 mm BG: schwarz / black R: regenbogen / rainbow
UFO-RB		35 358 20 Dichroic (U 60-56) 3,0 mm BG: schwarz / black R: regenbogen / rainbow
Quadrat-RB		35 359 20 Dichroic (U 60-56) 3,0 mm BG: schwarz / black R: regenbogen / rainbow

FLACHGLAS / FLAT GLASS



AK 90

35 370 00

Uroboros Dichroic Magic Box
16 Stücke, 10 x 5 cm, sortiert
Uroboros Dichroic magic box
16 pcs., 10 x 5 cm, assorted



AK 90

35 370 01

Uroboros Dichroic
Mustersatz
32 Muster 3,75 x 3,75 cm
Uroboros Dichroic sample set
32 samples 3,75 x 3,75 cm



AK 96

35 370 02

Uroboros Dichroic Magic Box96
10 Stücke, 10 x 5 cm, sortiert
Uroboros Dichroic magic box96
pcs., 10 x 5cm, assorted



AK 104

35 370 03

Moretti Mustersatz/
Moretti sample set
16 Stücke, 10 x 6,5 cm/
16 pieces 10 x 6,5cm



System 96

35 370 05

System 96 Glitzi Pack, 6 Stück Dichroic 5 x 10 cm
System 96 glitzi pack, 6 pieces Dichroic 5 x 10 cm




Goldbeschichtete Glastafeln,
Gold coated glass sheets,
3 mm

35 390 00 26 x 30 cm (Float)
35 392 00 20 x 30 cm (Artista)



Palladiumbeschichtete Glastafeln,
Palladium coated glass sheets,
3 mm

35 391 00 26 x 30 cm (Float)
35 393 00 20 x 30 cm (Artista)



AK 104

Moretti-Glasstäbe, Dichroic,
Moretti glass rods, Dichroic
40 cm

38 151 00 schwarz / black
38 151 01 klar / clear



AK 90

35 397 00

Dichro Stäbe / Stix
auf transparent
on transparent
10 Stck./pcs, 19 cm



AK 90

35 397 01

Dichro Stäbe / Stix
auf schwarz / on black
10 Stck./pcs, 19 cm



AK 104

35 397 03


Dichroic Streifen
Moretti, Bruchstücke transparent,
Dichroic stix clear Moretti Scrap
transparent




35 397 02 Dichroic Stäbe
klar Moretti
VE: 10 transparent 19 cm
Dichroic stix clear Moretti
VE: 10 transparent 19 cm
35 397 07 AK 104
Dichroic Streifen Moretti
30 cm transparent,
Dichroic stix Moretti,
30 cm transparent,




35 703 00
Dichroic Stringer
transparent/regenbogen
20 Stck. ø 1mm, 45 cm
Dichroic Stringer
clear/rainbow
20 pieces ø 1mm, 45 cm




35 703 01
Dichroic Stringer
transparent/regenbogen
50 Stck. ø 1mm, 45 cm
Dichroic Stringer
clear/rainbow
50 pieces ø 1mm, 45 cm




35 703 03
Dichroic STIX
Dichroic auf schwarz
18 Stck. ø 3mm, 40 cm
Dichroic STIX
Dichroic on black
18 pieces, ø 3mm, 40 cm




35 703 05
Dichroic Stringer
schwarz/regenbogen
20 Stck. ø 1mm, 45 cm
Dichroic Stringer
black/rainbow
20 pieces, ø 1mm, 45 cm




35 703 06
Dichroic STIX
Dichroic auf schwarz
12 Stck. ø 6mm, 40 cm
Dichroic STIX
Dichroic on black
12 pieces ø 6mm, 40 cm




35 703 13
Dichroic STIX
Dichroic auf klar
18 Stck. ø 3mm, 40 cm
Dichroic STIX
Dichroic on clear
18 pieces ø 3mm, 40 cm




35 703 16
Dichroic STIX
Dichroic auf klar
12 Stck. ø 6mm, 40 cm
Dichroic STIX
Dichroic on clear
12 pieces ø 6mm, 40 cm




35 704 03
Dichroic STIX
Dichroic regenbogen
18 Stck. ø 3mm, 40 cm
Dichroic STIX
Dichroic rainbow
18 pieces ø 3mm, 40 cm



35 704 06
Dichroic STIX
Dichroic regenbogen
12 Stck. ø 6mm, 40 cm
Dichroic STIX
Dichroic rainbow
12 pieces ø 6mm, 40 cm



35 704 13
Dichroic STIX
Dichroic klar regenbogen
18 Stck. ø 3mm, 40 cm
Dichroic STIX
Dichroic rainbow
18 pieces ø 3mm, 40 cm



35 704 16
Dichroic STIX
Dichroic klar regenbogen
12 Stck. ø 6mm, 40 cm
Dichroic STIX
Dichroic rainbow
12 pieces ø 6mm, 40 cm